




SENSORS




LUMI-TAU-INLINE-SL-IR/IR



LUMI-TAU-INLINE-SL-UV/BL
LUMI-TAU-INLINE-SL-BL/IR
LUMI-TAU-INLINE-SL-GN/IR



LUMI-TAU-INLINE-SL-R/IR



SPECTRO-T-1-10-DIF-UV/BL
SPECTRO-T-1-10-DIF-BL/YL
SPECTRO-T-1-10-DIF-R/IR
SPECTRO-T-1-10-DIF-BL/IR

MOBILE DEVICES



LUMI-TAU-IR/IR-MOBILE-P
LUMI-TAU-R/IR-MOBILE-P
LUMI-TAU-BL/IR-MOBILE-P
LUMI-TAU-UV/BL-MOBILE-P
LUMI-TAU-GN/IR-MOBILE-P

SPECTRO-T-1-DIF/0°-UV/BL-MOBILE-P
SPECTRO-T-1-DIF/0°-BL/YL-MOBILE-P
SPECTRO-T-1-DIF/0°-R/IR-MOBILE-P
SPECTRO-T-1-DIF/0°-BL/IR-MOBILE-P

LAB DEVICES

LUMI-TAU-IR/IR-LAB-LF
LUMI-TAU-R/IR-LAB-LF
LUMI-TAU-BL/IR-LAB-LF
LUMI-TAU-UV/BL-LAB-LF
LUMI-TAU-GN/IR-LAB-LF



SPECTRO-T-1-DIF/0°-UV/BL-LAB-LF
SPECTRO-T-1-DIF/0°-BL/YL-LAB-LF
SPECTRO-T-1-DIF/0°-R/IR-LAB-LF
SPECTRO-T-1-DIF/0°-BL/IR-LAB-LF



LUMI-TAU-IR/IR-LAB-CMU
LUMI-TAU-R/IR-LAB-CMU
LUMI-TAU-BL/IR-LAB-CMU
LUMI-TAU-UV/BL-LAB-CMU
LUMI-TAU-GN/IR-LAB-CMU



CALIB-LUMI-TAU



CALIB-SPECTRO-T-1



SPECTRO-T-1-DIF/0°-UV/BL-LAB-CMU
SPECTRO-T-1-DIF/0°-BL/YL-LAB-CMU
SPECTRO-T-1-DIF/0°-R/IR-LAB-CMU
SPECTRO-T-1-DIF/0°-BL/IR-LAB-CMU

INLINE DEVICES



SPECTRO-T-1-DIF/0°-UV/BL-INLINE
SPECTRO-T-1-DIF/0°-BL/YL-INLINE
SPECTRO-T-1-DIF/0°-R/IR-INLINE
SPECTRO-T-1-DIF/0°-BL/IR-INLINE



LUMI-TAU-IR/IR-INLINE
LUMI-TAU-R/IR-INLINE
LUMI-TAU-BL/IR-INLINE
LUMI-TAU-UV/BL-INLINE
LUMI-TAU-GN/IR-INLINE



SI-PPC-500-15"